

## 204XD3

Designed for handling and transport of contaminated and/or polluted instruments to be washed and then sterilized, and delivered back to departments.



Anti-torsion base chassis made of AISI 304 (1.4301) stainless steel tubes welded using a robotized TIG process; external edge with smoke grey PEHD. Equipped with 4 wheels diam. 160 mm non-marking gray rubber wheels with stainless steel roller bearings, 2 fixed and 2 swiveling with pedal operated brake, located at the corners. Trolley body made of 10/10 thick, brushed AISI 304 (1.4301) stainless steel sheet, suitably ribbed and reinforced. Ribbed pyramid roof to facilitate water drainage. Box section doors made of two sheets sandwich; surrounded by an interchangeable silicone rubber profile, as seal. The doors can be blocked in opening position at 270° and 255° to allow perfect cleaning of all internal and external surfaces. Equipped with 4 vertical 25 mm diam. push handles in tube located on the corners.

Inside compartment equipped with 3 DINNORM size container (600x300) holding columns each of which with 8 pairs of fixed guides every 125 mm.

Internal Height	Internal Width	Internal Depth	External Height	External Width	External Depth	Position	Ring Size	Diameter Wheels
1150	1050	640	1470	1260	710	0	0	160